

Granite Surface Plate, DIN 876

Item number: 901-122

Images



Description

- Surface diamond lapped, side face fine ground, backside fine sawn.
- The optional stand is a welded construction including 3 or 5-point bearings and two adjusting screws.
- Delivered with a certificate of inspection

Features

Vickers hardness:	HV 850-900
Flexural strength:	13-22 N/mm ²
Compressive strength:	Approx. 280 N/mm ²
Linear coefficient of expansion:	$(5 - 7.5) \times 10^{-6} \times K^{-1}$
Dimensions L x W x H:	400 x 400 x 50 mm
Accuracy:	DIN 876 grade 0
Max. workpiece load:	120 kg
Delivered:	With steel ball inserts and certificate of inspection
Mass:	25 kg

Dimensions

