

## Granite Surface Plate, DIN 876

Item number: 901-124

### Images




### Description

- Surface diamond lapped, side face fine ground, backside fine sawn.
- The optional stand is a welded construction including 3 or 5-point bearings and two adjusting screws.
- Delivered with a certificate of inspection

### Features

<b>Vickers hardness:</b>	HV 850-900
<b>Flexural strength:</b>	13-22 N/mm <sup>2</sup>
<b>Compressive strength:</b>	Approx. 280 N/mm <sup>2</sup>
<b>Linear coefficient of expansion:</b>	$(5 - 7.5) \times 10^{-6} \times K^{-1}$
<b>Dimensions L x W x H:</b>	630 x 630 x 70 mm
<b>Accuracy:</b>	DIN 876 grade 0
<b>Max. workpiece load:</b>	150 kg
<b>Delivered:</b>	With steel ball inserts and certificate of inspection
<b>Mass:</b>	83 kg

### Dimensions



### Accessories

Optional accessories:



## Stand (Angle Steel), Granite Plate

630x630x70mm

Art No. 901-932

Suggested retail price: 571.00 €\*  

---