

Digital Precision Level

Item number: 950-318

Images



Description

A high-resolution Mitutoyo digital protractor/level designed for making precise angle measurements in the vertical plane. The instrument can be zeroed at any angular position and directly indicates the angle between the stock and that position when in use to a resolution of 0.01 degree over a range of +/- 10 degrees (0.1 degree over the remainder of the range). When zeroed at the horizontal, readings are provided in the same manner as a spirit level, but with the advantage of a range extending all the way to the vertical.

Features

Range:	360° (4 x 90°)
Max. permissible error (degrees):	0.05 (0 to 10) 0.1 (80 to 90) 0.2 (10 to 80)
Repeatability (degrees):	0.05
Power supply:	Standard battery (9 V) 6LR61
Data output:	Yes
Battery life:	Approx. 500 hours
Sensitivity (degrees):	0.01 (0 to 9.99) 0.1 (10 to 90)
Delivered:	Including box
Mass:	0.3 kg

Accessories

Proposed additional product:



RS-232C Output Cable

for series 950
Art No. 50AAA983A
Suggested retail price: 650.00 €*

Promotion!

Mitutoyo

MICAT
the standard in world
metrology software
MeasurLink®

USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available
Online)

Art No. 06AGR543

Promo price: 268.00 €*

Suggested retail price: 340.00 €*

