

**MODLINK MSDD DATA INSERT**

1xSUB-D9 fem./soldering + 1xSUB-D9 male/soldering

SUB-D9; SUB-D9

1 × SUB-D9 (solder connection/female)

1 × SUB-D9 (solder connection/male)

**Illustration**

Product may differ from Image

**Approvals****General data**

Dimensions H×W×D 88×51×40 mm

**SUB-D9**

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (solder connection)
Locking of ports	UNC 4...40 bolt

**Shielding plate**

Connection	Threaded hole M4
Tightening torque	0.9 Nm ±0.1

**Commercial data**

country of origin	DE
customs tariff number	85366990
EAN	4048879038089
eClass	27189217

Packaging unit 1

