

MODLINK MSDD DATA INSERT

1xSUB-D9 male/soldering + 1xSUB-D25 fem./soldering

SUB-D9; SUB-D25

1 × SUB-D9 (solder connection/male)

1 × SUB-D25 (solder connection/female)

Illustration

Product may differ from Image

Approvals**General data**

Dimensions H×W×D 88×51×40 mm

SUB-D25

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	25-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (solder connection)
Locking of ports	UNC 4...40 bolt

SUB-D9

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (male)
Connection rear side	SUB-D (solder connection)
Locking of ports	UNC 4...40 bolt

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879037983
eClass	27189217
Packaging unit	1