

MODLINK MSDD DATA INSERT

2xSUB-D15 female/male

SUB-D15; SUB-D15
2x SUB-D15 (female/male)

Illustration

Product may differ from Image

Approvals**General data**

Dimensions H×W×D 88×51×40 mm

SUB-D15 HD

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	15-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (male)
Locking of ports	UNC 4...40 bolt

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879037969
eClass	27189217
Packaging unit	1