

MODLINK MSDD DATA INSERT

1xSUB-D15 female/soldering + 1xSUB-D9 blind

SUB-D15

1 × SUB-D15 (solder connection/female)

1 × SUB-D9 (blind plug)

Illustration

Product may differ from Image

Approvals**General data**

Dimensions H×W×D	88×51×40 mm
------------------	-------------

SUB-D15 HD

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
-------------------------------	------------------------

Operating current (UL Rating)	max. 175 mA
-------------------------------	-------------

No. of poles	15-pole
--------------	---------

Connection front side	SUB-D (female)
-----------------------	----------------

Connection rear side	SUB-D (solder connection)
----------------------	---------------------------

Locking of ports	UNC 4...40 bolt
------------------	-----------------

Commercial data

country of origin	DE
-------------------	----

customs tariff number	85366990
-----------------------	----------

EAN	4048879037945
-----	---------------

eClass	27189217
--------	----------

Packaging unit	1
----------------	---