

**MODLINK MSDD DATA INSERT**

2×USB-A female/female

USB (form A); USB (form A)  
2× USB (female/female) form A

**Illustration**

Product may differ from Image

**Approvals****General data**

Dimensions H×W×D	88×51×70.4 mm
------------------	---------------

**Shielding plate**

Connection	Threaded hole M4
------------	------------------

Tightening torque	0.9 Nm ±0.1
-------------------	-------------

**USB**

Operating voltage	48 V AC/DC
-------------------	------------

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
-------------------------------	------------------------

Operating current	1.5 A
-------------------	-------

Locking of ports	Snap In
------------------	---------

Specification	USB: 3.0 (max. 5 Gbit/s)
---------------	--------------------------

**Commercial data**

country of origin	CZ
-------------------	----

customs tariff number	85366990
-----------------------	----------

EAN	4048879037815
-----	---------------

eClass	27189217
--------	----------

Packaging unit	1
----------------	---