

**MODLINK MSDD DATA INSERT**

1xUSB-A female/female + 1xSUB-D25 female/male

USB (form A); SUB-D25

1 × USB 3.0 (female/female) form A

1 × SUB-D25 (female/male)

**Illustration**

Product may differ from Image

**Approvals****General data**

Dimensions H×W×D 88×51×70.4 mm

**SUB-D25**

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	25-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (male)
Locking of ports	UNC 4...40 bolt

**Shielding plate**

Connection	Threaded hole M4
Tightening torque	0.9 Nm ±0.1

**USB**

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	1.5 A
Locking of ports	Snap In
Specification	USB: 3.0 (max. 5 Gbit/s)

**Commercial data**

country of origin	DE
customs tariff number	85366990
EAN	4048879037730
eClass	27189217
Packaging unit	1