

**MODLINK MSDD DATA INSERT**

1×SUB-D9fem./fem.+1×SUB-D9male/male+1×RJ45+1×USB-A

RJ45; USB (A); SUB-D9; SUB-D9

1× RJ45, 8-pole metal, CAT5e (female/female)

1× USB 2.0 (female/female) form A

1× SUB-D9 (female/female)

1× SUB-D9 (male/male)

**Illustration**

Product may differ from Image

**General data**

Dimensions H×W×D 88×51×45 mm

**SUB-D9**

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (female)
Locking of ports	UNC 4...40 bolt

**RJ45**

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current (UL Rating)	max. 175 mA
Connection front side	RJ45
Connection rear side	RJ45
Locking of ports	Snap In
Specification	CAT5e, Class D, 100 MHz, (EN 50173-1)

**Shielding plate**

Connection	Threaded hole M4
Tightening torque	0.9 Nm ±0.1

**USB**

Operating voltage	48 V AC/DC
-------------------	------------

Operating voltage (UL Rating)	42.4 V DC
Operating current	max. 500 mA
Locking of ports	Snap In
Specification	USB: 2.0 (max. 480 Mbit/s)

**Commercial data**

country of origin	DE
customs tariff number	85366990
EAN	4048879037631
eClass	27189217
Packaging unit	1