

MODLINK MSDD DATA INSERT

2×RJ45

RJ45; RJ45

2× RJ45, 8-pole metal, CAT5e (female/female)

Illustration

Product may differ from Image

Approvals**General data**

Dimensions H×W×D	88×51×21 mm
------------------	-------------

RJ45

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current (UL Rating)	max. 175 mA
Connection front side	RJ45
Connection rear side	RJ45
Locking of ports	Snap In
Specification	CAT5e, Class D, 100 MHz, (EN 50173-1)

Shielding plate

Connection	Threaded hole M4
Tightening torque	0.9 Nm ±0.1

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879037624
eClass	27189217
Packaging unit	1