

MODLINK MSDD DATA INSERT

1×SUB-D9 female/female + 1×RJ45 + 1×RJ12 + 1×USB-A

RJ45; RJ12; USB; USB (A); SUB-D9

1× RJ45, 8-pole metal, CAT5e (female/female)

1× RJ12 (6-pole plastic)

1× USB 2.0 (female/female) form A

1× SUB-D9 (female/female)

Illustration

Product may differ from Image

General data

Dimensions H×W×D 88×51×45 mm

SUB-D9

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (female)
Locking of ports	UNC 4...40 bolt

RJ45

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current (UL Rating)	max. 175 mA
Connection front side	RJ45
Connection rear side	RJ45
Locking of ports	Snap In
Specification	CAT5e, Class D, 100 MHz, (EN 50173-1)

RJ12

Operating voltage	max. 48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	max. 1 A
Operating current (UL Rating)	max. 175 mA
Connection front side	RJ12

Connection rear side	RJ12
Locking of ports	Snap In
Shielding plate	
Connection	Threaded hole M4
Tightening torque	0.9 Nm \pm 0.1
USB	
Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	42.4 V DC
Operating current	max. 500 mA
Locking of ports	Snap In
Specification	USB: 2.0 (max. 480 Mbit/s)
Commercial data	
country of origin	DE
customs tariff number	85366990
EAN	4048879310116
eClass	27189217
Packaging unit	1