

MODLINK MSDD DATA INSERT

1×SUB-D25 female/male + 1×RJ45

SUB-D25; RJ45; USB (pre-cut)

1× SUB-D25 (female/male)

1× RJ45, 8-pole metal, CAT5e (female/female)

1× USB (pre-cut)

shielded

Illustration

Product may differ from Image

General data

Dimensions H×W×D	88×51×21 mm
------------------	-------------

SUB-D25

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	25-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (male)
Locking of ports	UNC 4...40 bolt

RJ45

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current (UL Rating)	max. 175 mA
Connection front side	RJ45
Connection rear side	RJ45
Locking of ports	Snap In
Specification	CAT5e, Class D, 100 MHz, (EN 50173-1)

Shielding plate

Connection	Threaded hole M4
Tightening torque	0.9 Nm ±0.1

Commercial data

country of origin	DE
-------------------	----

customs tariff number	85366990
EAN	4048879037426
eClass	27189217
Packaging unit	1