

MODLINK MSDD DATA INSERT

1×SUB-D9 female/male + 2×RJ45

RJ45; RJ45; SUB-D9

2× RJ45, 8-pole metal, CAT5e (female/female)

1× SUB-D9 (female/male)

Illustration

Product may differ from Image

General data

Dimensions H×W×D	88×51×21 mm
------------------	-------------

SUB-D9

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (male)
Locking of ports	UNC 4...40 bolt

RJ45

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current (UL Rating)	max. 175 mA
Connection front side	RJ45
Connection rear side	RJ45
Locking of ports	Snap In
Specification	CAT5e, Class D, 100 MHz, (EN 50173-1)

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879037419
eClass	27189217
Packaging unit	1