MURR ELEKTRONIK
stay connected

MODLINK MSDD SINGLE COMBI INSERT USA NEMA 5-15

1xSUD-D9 female/female + 1xRJ45 female/female

1× NEMA 5-15 (plug-solder connection)
1× RJ45, 8-pole metal, CAT5e (female/female)
1× SUB-D9 (female/female)

Illustration



Product may differ from Image

Approvals

General data

Dimensions H×W×D	88×51×30 mm

SUB-D9

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (female)
Locking of ports	UNC 4...40 bolt

RJ45

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current (UL Rating)	max. 175 mA
Connection front side	RJ45
Connection rear side	RJ45
Locking of ports	Snap In
Specification	CAT5e, Class D, 100 MHz, (EN 50173-1)

USA

Operating voltage	125 V AC

The information in this brochure has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 10/20

Operating current	15 A
No. of poles	2 + PE
Connection	Plug-solder connection: 4.8×0.5 mm
Commercial data	
country of origin	DE
customs tariff number	85366990
EAN	4048879037235
eClass	27189217
Packaging unit	1

The information in this brochure has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 10/20