

MODLINK MSDD SINGLE COMBI INSERT USA NEMA 5-15

1xRJ45 female/female + 1x3A fuse

1 x NEMA 1-15 (plug-solder connection)

1 x RJ45, 8-pole metal, CAT5e (female/female)

1 x fuse (3 A)

Illustration

Product may differ from Image

Approvals**General data**

Dimensions H×W×D 88×51×53 mm

RJ45

Operating voltage (UL Rating) max. 30 V AC/42.4 V DC

Operating current (UL Rating) max. 175 mA

Connection front side RJ45

Connection rear side RJ45

Locking of ports Snap In

Specification CAT5e, Class D, 100 MHz, (EN 50173-1)

Shielding plate

Connection Threaded hole M4

Tightening torque 0.9 Nm ±0.1

Fuse

Operating voltage 250 V AC/32 V DC

Continuous load 3 A

USA

Operating voltage 125 V AC

Operating current 15 A

No. of poles 2 + PE

Connection Plug-solder connection: 4.8x0.5 mm

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879452762
eClass	27189217
Packaging unit	1