

MODLINK MSDD SINGLE COMBI INSERT FRANCE

2x data cutout

1× France (UTE-NF) white

2× RJ45 cut-out

Illustration

Product may differ from Image

General data

Protection	IP20
Dimensions H×W×D	87.5×50.7×43 mm (3.44×1.99×1.69 in)
Temperature range	-5...+50 °C
Storage temperature range	-10...+60 °C (14...140 °F)

Shielding plate

Connection	Threaded hole M4
Tightening torque	0.9 Nm ±0.1

France (UTE-NF)

Operating voltage	250 V AC
Operating current	16 A
No. of poles	2 + PE
Connection	Screw terminals: max. 2× 4 mm ² (AWG 12)

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879600897
eClass	27189217
Packaging unit	1