

MODLINK MSDD SINGLE COMBI INSERT FRANCE

1x RJ45 + 1x data cutout

1x France (UTE-NF) white

1x RJ45, 8-pole metal, CAT6A (female/female)

1x RJ45 cut-out

Illustration

Product may differ from Image

General data

Protection	IP20
Dimensions H×W×D	87.5×50.7×43 mm (3.44×1.99×1.69 in)
Temperature range	-5...+50 °C
Storage temperature range	-10...+60 °C (14...140 °F)

RJ45

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current (UL Rating)	max. 175 mA
Connection front side	RJ45
Connection rear side	RJ45
Locking of ports	Snap In
Specification	CAT6A

Shielding plate

Connection	Threaded hole M4
Tightening torque	0.9 Nm ±0.1

France (UTE-NF)

Operating voltage	250 V AC
Operating current	16 A
No. of poles	2 + PE
Connection	Screw terminals: max. 2× 4 mm² (AWG 12)

Commercial data

country of origin	LV
customs tariff number	85366990
EAN	4048879601009
eClass	27189217

Packaging unit

1