

MODLINK MSDD SINGLE COMBI INSERT ITALY

1x SUB-D9 ST/BU

1x Italy (CEI 23-16)

1x SUB-D9 (male/female)

1x SUB-D9 cut-out

Illustration

Product may differ from Image

General data

Protection	IP20
Dimensions H×W×D	87.5×50.7×30.7 mm (3.44×1.99×1.21 in)
Temperature range	-5...+50 °C
Storage temperature range	-10...+60 °C (14...140 °F)

SUB-D9

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (male)
Connection rear side	SUB-D (female)
Locking of ports	UNC 4...40 bolt

Shielding plate

Connection	Threaded hole M4
Tightening torque	0.9 Nm ±0.1

Italy (CEI 23-16)

Operating voltage	250 V AC
Operating current	16 A
No. of poles	2 + PE
Connection	Screw terminals: max. 2× 4 mm ² (AWG 12)

Commercial data

country of origin	HU
customs tariff number	85366990

EAN	4048879601054
eClass	27189217
Packaging unit	1