

MODLINK MSDD SINGLE COMBI INSERT BRAZIL

1x SUB-D9 ST/BU

1x Brazil

1x SUB-D9 (male/female)

1x SUB-D9 cut-out

Illustration

Product may differ from Image

General data

Protection	IP20
Dimensions H×W×D	87.5×50.7×30.7 mm (3.44×1.99×1.21 in)
Temperature range	+5...+35 °C
Storage temperature range	+5...+35 °C

SUB-D9

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (male)
Connection rear side	SUB-D (female)
Locking of ports	UNC 4...40 bolt

Shielding plate

Connection	Threaded hole M4
Tightening torque	0.9 Nm ±0.1

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879601160
eClass	27189217
Packaging unit	1