

MODLINK MSDD DATA INSERT

1xSUB-D9 male/soldering + 1xSUB-D9 blind

- 1 × SUB-D9 (solder connection/male)
- 1 × SUB-D9 (blind plug)

Illustration



Product may differ from Image

Approvals



General data

Dimensions H×W×D 88×51×40 mm

SUB-D9

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (male)
Connection rear side	SUB-D (solder connection)
Locking of ports	UNC 4...40 bolt

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879037174
eClass	27189217
Packaging unit	1