



**Modlink MSDD-set: Frame 4000-68112-0000000,**

insert 4000-68000-0510000

**Illustration**





Product may differ from Image

#### Frame

suitable for mounting with wall thickness	1...5 mm
Protection	IP65
Housing	Zinc die-casting, KTL coated
Temperature range	-10...+60 °C (storage temperature -25...+60 °C)

#### SUB-D15 HD

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current (UL Rating)	max. 175 mA
No. of poles	15-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (solder connection)
Locking of ports	UNC 4...40 bolt

#### Commercial data

country of origin	CZ
customs tariff number	85366990
EAN	4048879036535
eClass	27189217
Packaging unit	1