



**Modlink MSDD-set: Frame 4000-68112-0000000,**

insert 4000-68000-0940000

**Illustration**





Product may differ from Image

#### Frame

suitable for mounting with wall thickness	1...5 mm
Protection	IP65
Housing	Zinc die-casting, KTL coated
Temperature range	-10...+60 °C (storage temperature -25...+60 °C)

#### RJ45

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current (UL Rating)	max. 175 mA
Connection front side	RJ45
Connection rear side	RJ45
Locking of ports	Snap In
Specification	CAT5e, Class D, 100 MHz, (EN 50173-1)

#### Shielding plate

Connection	Threaded hole M4
Tightening torque	0.9 Nm ±0.1

#### USB

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	1.5 A
Locking of ports	Snap In
Specification	USB: 3.0 (max. 5 Gbit/s)

#### Commercial data

country of origin	CZ
customs tariff number	85366990
EAN	4048879379120
eClass	27189217
Packaging unit	1