

**Modlink MSDD-set: Frame 4000-68113-0000000,**

insert 4000-68000-0150000

### Illustration



Product may differ from Image

### Frame

suitable for mounting with wall thickness	1...5 mm
Protection	IP65

Housing	Zinc die-casting, with surface finishing
Temperature range	-10...+60 °C (storage temperature -25...+60 °C)

**France (UTE-NF)**

Operating voltage	250 V AC
Operating current	10...16 A
No. of poles	2 + PE
Connection	Spring clamp terminals: max. 2× 2.5 mm <sup>2</sup> (AWG 14)

**Commercial data**

country of origin	CZ
customs tariff number	85366990
EAN	4048879332118
eClass	27189217
Packaging unit	1