

**Modlink MSDD-set: Frame 4000-68113-0000000,**

insert 4000-68000-0220000

### Illustration



Product may differ from Image

### Frame

suitable for mounting with wall thickness	1...5 mm
Protection	IP65

Housing	Zinc die-casting, with surface finishing
Temperature range	-10...+60 °C (storage temperature -25...+60 °C)

**SUB-D9**

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (male)
Connection rear side	SUB-D (solder connection)
Locking of ports	UNC 4...40 bolt

**Commercial data**

country of origin	CZ
customs tariff number	85389099
EAN	4048879036269
eClass	27189217
Packaging unit	1