



Modlink MSDD-set: Frame 4000-68113-000000,

insert 4000-68000-071000

Illustration





Product may differ from Image

Frame

| | |
|---|---|
| suitable for mounting with wall thickness | 1...5 mm |
| Protection | IP65 |
| Housing | Zinc die-casting, with surface finishing |
| Temperature range | -10...+60 °C (storage temperature -25...+60 °C) |

SUB-D25

| | |
|-------------------------------|---------------------------|
| Operating voltage | 48 V AC/DC |
| Operating voltage (UL Rating) | max. 30 V AC/42.4 V DC |
| Operating current | 3 A |
| Operating current (UL Rating) | max. 175 mA |
| No. of poles | 25-pole |
| Connection front side | SUB-D (female) |
| Connection rear side | SUB-D (solder connection) |
| Locking of ports | UNC 4...40 bolt |

Commercial data

| | |
|-----------------------|---------------|
| country of origin | CZ |
| customs tariff number | 85389099 |
| EAN | 4048879036207 |
| eClass | 27189217 |
| Packaging unit | 1 |