

Modlink MSDD-set: Frame 4000-68113-000000,

insert 4000-68000-0800000

Illustration



Product may differ from Image

Frame

suitable for mounting with wall thickness	1...5 mm
Protection	IP65

Housing	Zinc die-casting, with surface finishing
Temperature range	-10...+60 °C (storage temperature -25...+60 °C)

SUB-D15 HD

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	15-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (male)
Locking of ports	UNC 4...40 bolt

PS2

Operating voltage	30 V AC/DC
Operating current	1 A
No. of poles	6-pole
Connection cross section	max. 0.5 mm ² (AWG 20)
Connection front side	PS2 (female)
Connection rear side	PS2 (solder connection)
Locking of ports	Screw locking

Commercial data

country of origin	CZ
customs tariff number	85366990
EAN	4048879036177
eClass	27189217
Packaging unit	1