


Modlink MSDD-set: Frame 4000-68113-0000000,

insert 4000-68000-3010000

Illustration





Product may differ from Image

Frame

suitable for mounting with wall thickness	1...5 mm
Protection	IP65
Housing	Zinc die-casting, with surface finishing
Temperature range	-10...+60 °C (storage temperature -25...+60 °C)

France (UTE-NF)

Operating voltage	250 V AC
Operating current	16 A
No. of poles	2 + PE
Connection	Screw terminals: max. 2× 4 mm ² (AWG 12)

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879513289
eClass	27189217
Packaging unit	1