

Modlink MSDD-set: Frame 4000-68122-0000000,
insert 4000-68000-1200000 + 4000-68000-0010000

Illustration

Product may differ from Image

Frame

suitable for mounting with wall thickness	1...5 mm
Protection	IP65
Housing	Zinc die-casting, KTL coated

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 10/20

Temperature range -10...+60 °C (storage temperature -25...+60 °C)

RJ45

Operating voltage (UL Rating) max. 30 V AC/42.4 V DC

Operating current (UL Rating) max. 175 mA

Connection front side RJ45

Connection rear side RJ45

Locking of ports Snap In

Specification CAT5e, Class D, 100 MHz, (EN 50173-1)

Shielding plate

Connection Threaded hole M4

Tightening torque 0.9 Nm ±0.1

Germany (VDE)

Operating voltage 250 V AC

Operating current 16 A

No. of poles 2 + PE

Connection Screw terminals: max. 2× 6 mm² (AWG 10)

LED display yellow

Commercial data

country of origin CZ

customs tariff number 85389099

EAN 4048879035422

eClass 27189217

Packaging unit 1