



Modlink MSDD-set: Frame 4000-68123-0000000,
insert 4000-68000-3250000 + 4000-68000-1410000

Illustration



Product may differ from Image

Frame

suitable for mounting with wall thickness	1...5 mm
Protection	IP65
Housing	Zinc die-casting, with surface finishing
Temperature range	-10...+60 °C (storage temperature -25...+60 °C)

SUB-D9

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (female)
Locking of ports	UNC 4...40 bolt

RJ45

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current (UL Rating)	max. 175 mA
Connection front side	RJ45
Connection rear side	RJ45
Locking of ports	Snap In
Specification	CAT5e, Class D, 100 MHz, (EN 50173-1)

Shielding plate

Connection	Threaded hole M4
Tightening torque	0.9 Nm $\pm$ 0.1

China (CCC)

Operating voltage	250 V AC
-------------------	----------

Operating current	10 A
No. of poles	2 + PE
Connection	Screw terminals: max. 2× 4 mm ² (single/stranded wire)

Commercial data

country of origin	DE
customs tariff number	85389099
EAN	4048879330671
eClass	27189217
Packaging unit	1