

Modlink MSDD-set: Frame 4000-68223-0000000,
insert 4000-68000-0200000 + 4000-68000-0020000

Illustration



Product may differ from Image

Frame

suitable for mounting with wall thickness 1...5 mm

Protection IP65

Housing Frame: zinc die-casting, with surface finishing, Lid: plastic, PC transparent

Temperature range -10...+60 °C (storage temperature -25...+60 °C)

SUB-D9

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (male)
Locking of ports	UNC 4...40 bolt

Germany (VDE)

Operating voltage	250 V AC
Operating current	16 A
No. of poles	2 + PE
Connection	Screw terminals: max. 2× 6 mm ² (AWG 10)

Commercial data

country of origin	CZ
customs tariff number	85389099
EAN	4048879032827
eClass	27189217
Packaging unit	1