

Modlink MSDD-set: Frame 4000-68223-0000000,
insert 4000-68000-0410000 + 4000-68000-3210000

Illustration



Product may differ from Image

Frame	
suitable for mounting with wall thickness	1...5 mm
Protection	IP65
Housing	Frame: zinc die-casting, with surface finishing, Lid: plastic, PC transparent

Temperature range -10...+60 °C (storage temperature -25...+60 °C)

SUB-D25

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	25-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (solder connection)
Locking of ports	UNC 4...40 bolt

SUB-D9

Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
Operating current (UL Rating)	max. 175 mA
No. of poles	9-pole
Connection front side	SUB-D (female)
Connection rear side	SUB-D (solder connection)
Locking of ports	UNC 4...40 bolt

India (IS 1293)

Operating voltage	240 V AC
Operating current	5 A
No. of poles	2 + PE
Connection	Screw terminals: max. 2× 1.5 mm ² (AWG 16)

Commercial data

country of origin	CZ
customs tariff number	85366990
EAN	4048879340106
eClass	27189217
Packaging unit	1