

**Modlink MSDD-set: Frame 4000-68223-0000000,**  
insert 4000-68000-0900000 + 4000-68000-0030000

Illustration



Product may differ from Image

| Frame                                     |                                                                               |
|-------------------------------------------|-------------------------------------------------------------------------------|
| suitable for mounting with wall thickness | 1...5 mm                                                                      |
| Protection                                | IP65                                                                          |
| Housing                                   | Frame: zinc die-casting, with surface finishing, Lid: plastic, PC transparent |

Temperature range -10...+60 °C (storage temperature -25...+60 °C)

**USB**

|                               |                            |
|-------------------------------|----------------------------|
| Operating voltage             | 48 V AC/DC                 |
| Operating voltage (UL Rating) | 42.4 V DC                  |
| Operating current             | max. 500 mA                |
| Locking of ports              | Snap In                    |
| Specification                 | USB: 2.0 (max. 480 Mbit/s) |

**USA**

|                   |                                    |
|-------------------|------------------------------------|
| Operating voltage | 125 V AC                           |
| Operating current | 15 A                               |
| No. of poles      | 2 + PE                             |
| Connection        | Plug-solder connection: 4.8×0.5 mm |

**Commercial data**

|                       |               |
|-----------------------|---------------|
| country of origin     | CZ            |
| customs tariff number | 85366990      |
| EAN                   | 4048879032643 |
| eClass                | 27189217      |
| Packaging unit        | 1             |