

**Modlink MSDD-set: Frame 4000-68223-0000000,**  
insert 4000-68000-1200000 + 4000-68000-1260000

### Illustration



Product may differ from Image

### Frame

suitable for mounting with wall thickness 1...5 mm

Protection IP65

Housing Frame: zinc die-casting, with surface finishing, Lid: plastic, PC transparent

Temperature range -10...+60 °C (storage temperature -25...+60 °C)

#### Panel jack SLB4

Operating voltage (UL Rating) max. 30 V AC/42.4 V DC

Operating current 24 A

Connection Flat connector 4.8×0.8 mm

#### RJ45

Operating voltage (UL Rating) max. 30 V AC/42.4 V DC

Operating current (UL Rating) max. 175 mA

Connection front side RJ45

Connection rear side RJ45

Locking of ports Snap In

Specification CAT5e, Class D, 100 MHz, (EN 50173-1)

#### Shielding plate

Connection Threaded hole M4

Tightening torque 0.9 Nm ±0.1

#### Commercial data

country of origin CZ

customs tariff number 85366990

EAN 4048879330732

eClass 27189217

Packaging unit 1