

MODLINK MSDD CABLE ENTRY SYSTEM

KDP/R

round (M50)

Cable diameter (7)× 3...6.5 mm, (1)× 6...10 mm

For sale only in packing units

Illustration

Product may differ from Image

Approvals**General data**

Dimensions H×W×D	33×58×58 mm
Cut-out	50.5×50.5
Mounting method	DIN-rail mounting or screw mounting via locknut (wall thickness 1.5...2.0 mm)
Temperature range	-30...+70 °C

Technical Data

Sealing range (cable Ø)	Cable diameter (7)× 3...6.5 mm, (1)× 6...10 mm
Protection	IP65
Housing	Polyamide

Commercial data

country of origin	DE
customs tariff number	39269097
EAN	4048879031615
eClass	27189217
Packaging unit	1