

MODLINK MSDD CABLE ENTRY SYSTEM

KDP/R

round (M63)

Cable diameter (2)× 3...6.5 mm, (4)× 5...9.2 mm, (2)× 9.6...15.9 mm

For sale only in packing units

Illustration

Product may differ from Image

Approvals**General data**

Mounting method	DIN-rail mounting or screw mounting via locknut (wall thickness 1.5...2.0 mm)
Dimensions H×W×D	34×71×71 mm
Cut-out	63.5×63.5
Temperature range	-30...+70 °C

Technical Data

Sealing range (cable Ø)	Cable diameter (2)× 3...6.5 mm, (4)× 5...9.2 mm, (2)× 9.6...15.9 mm
Protection	IP65
Housing	Polyamide

Commercial data

country of origin	DE
customs tariff number	39269097
EAN	4048879031608
eClass	27189217
Packaging unit	1