

AIDA PUSH PULL COUPLING HAN24

with power (5 pole) spring clamp + RJ45 fem/fem

with RJ45 and energy

1 × RJ45, 8-pole metal, CAT5e (female/female)

Combicon Power/spring clamp terminal, Push Pull

Size 24

Illustration

Product may differ from Image

General data

Temperature range	-25...+70 °C
Dimensions H×W×D	146×58×65 mm

Technical Data

Protection	IP65
Material	PA

Commercial data

country of origin	CZ
customs tariff number	85366990
EAN	4048879031165
eClass	27143423
Packaging unit	1