

AIDA PUSH PULL COUPLING HAN24

with power (5 pole) spring clamp + SCRJ

with fiber optic and energy

Combicon Power/spring clamp terminal, Push Pull
Size 24**Illustration**

Product may differ from Image

General data

Temperature range	-25...+70 °C
Dimensions H×W×D	146×58×52 mm

Technical Data

Protection	IP65
Material	PA

Commercial data

country of origin	CZ
customs tariff number	85366990
EAN	4048879031158
eClass	27143423
Packaging unit	1