

Modlight50 Pro LED modul blue

Input 24VDC

LED module (blue)

Illustration

Product may differ from Image

General data

Protection	IP65 inserted and tightened (EN 60529)
Connection	Notched contact
Housing	Plastic, PC
Dimensions H×W×D	52×50×50 mm
Temperature range	-30...+60 °C

Technical Data

Operating voltage	24 V DC (21.6...26.4 V DC)
Current consumption	max. 62.5 mA

Commercial data

country of origin	ID
customs tariff number	85319000
EAN	4048879751537
eClass	27371200
Packaging unit	1