

Modlight70 Pro LED modul red

Input 24VDC

LED module (red)

Illustration

Product may differ from Image

General data

Protection	IP65 inserted and tightened (EN 60529)
Dimensions H×W×D	49×70×70 mm
Connection	Notched contact
Housing	Plastic, PC
Temperature range	-30...+60 °C

Technical Data

Operating voltage	24 V DC (21.6...26.4 V DC)
Current consumption	max. 62.5 mA

Commercial data

country of origin	ID
customs tariff number	85319000
EAN	4048879752626
eClass	27371200
Packaging unit	1