


M12 MALE 0° / M12 FEMALE 0° SHIELDED

PUR 4X0.34 shielded GRAY, 13m


Male straight – female straight  
M12 – M12, 4-pole  
shielded  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

Illustration



Product may differ from Image

Approvals



\* only for products with UL/CSA approved cable

cCSAus

Form

Form 40501

Cables

|                       |                          |
|-----------------------|--------------------------|
| Cable number          | 331                      |
| No./diameter of wires | 4 x 0.34 mm <sup>2</sup> |
| Wire isolation        | PVC (br, wh, bl, bk)     |
| Jacket Color          | gray                     |
| Material (jacket)     | PUR/PVC                  |
| Outer Ø               | 5.9 mm ±5%               |

|                            |              |
|----------------------------|--------------|
| Bend radius (fixed)        | 10× outer Ø  |
| Bend radius (moving)       | 15× outer Ø  |
| Temperature range (fixed)  | -30...+80 °C |
| Temperature range (mobile) | -5...+70 °C  |
| Shield                     | yes          |
| Color (jacket)             | gray         |
| Approval (cable)           | CE conform   |

**Technical Data**


|                                    |                                                                  |
|------------------------------------|------------------------------------------------------------------|
| Operating voltage                  | max. 60 V AC/DC                                                  |
| Operating voltage (only UL listed) | max. 30 V AC/DC                                                  |
| Operating current per contact      | max. 4 A                                                         |
| Locking of ports                   | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing |
| Compression gland                  | M12 (SW13)                                                       |
| Locking material                   | Zinc die casting, matte nickel plated                            |
| Protection                         | IP65 and IP67 when plugged and screwed down (EN 60529)           |

**General data**

|                   |                                          |
|-------------------|------------------------------------------|
| Standards         | DIN EN 61076-2-101 (M12)                 |
| Temperature range | -25...+85 °C, depending on cable quality |


**Commercial data**

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444290      |
| EAN                   | 4048879381758 |
| eClass                | 27279218      |
| Packaging unit        | 1             |

**Sketch**

Male

Female



Product may differ from Image