

adaptor M12 male 3pol. / M12 female 4pol.

Adapter
Male - female
M12 – M12
3-/4-pole

Illustration

Product may differ from Image

Approvals**Form**

Form	41242
------	-------

Technical Data

Operating voltage	max. 250 V AC/DC
Operating voltage (only UL listed)	max. 30 V AC/DC
Rated surge voltage	2.5 kV
Operating current per contact	max. 4 A
Material group	IEC 60664-1, category I
Locking of ports	Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing
Compression gland	M12 (SW13)
Protection	IP67 inserted and tightened (EN 60529)
Locking material	Zinc die casting, matte nickel plated
Material	PUR


General data

Pollution Degree	3
Mounting method	inserted, tightened
Temperature range	-25...+85 °C

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879404310
eClass	27143423
Packaging unit	1

Sketch



Product may differ from Image