

**M12 MALE ON REAR OF MSUD VALVE PLUG FORM B 10 MM**

Form B (10 mm) – M12, connector at the rear

24 V AC  $\pm 20\%$  / DC  $\pm 25\%$

LED and suppression

3-pole

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.



**Illustration**

*stay connected*




Female

Male



Depth: 22 mm



Product may differ from Image

**Approvals**

**Form**

Form 41961

**Technical Data**

Operating voltage	24 V AC $\pm 20\%$ / DC $\pm 25\%$
Rated surge voltage	0.8 kV
Operating current per contact	max. 4 A
Configuration	2 contacts + PE
Locking of ports	M3/M12 $\times$ 1 mm (recommended torque 0.4/0.6 Nm)
Protection	IP67 inserted and tightened (EN 60529)

**General data**

Temperature range -25...+85 °C

**Commercial data**

country of origin	CZ
customs tariff number	85366990
EAN	4048879143349
eClass	27143423
Packaging unit	1