

M12 MALE ON REAR OF MSUD VALVE PLUG FORM BI 11MM

Form BI (11 mm) – M12, connector at the rear

24 V AC/DC $\pm 25\%$

LED

3-pole

Plastic housings with good resistance against chemicals and oils.




The resistance to aggressive media should be individually tested for your application. Further details on request.

Illustration



Female

Male



Product may differ from Image

Approvals

**Form**

Form	42061
------	-------

Technical Data

Operating voltage	24 V AC/DC $\pm 25\%$
Operating current per contact	max. 4 A
Configuration	2 contacts + PE
Protection	IP67 inserted and tightened (EN 60529)
Locking of ports	M3/M12 $\times$ 1 mm (recommended torque 0.4/0.6 Nm)

General data

Temperature range	-25...+85 °C
-------------------	--------------

Commercial data

country of origin	CZ
customs tariff number	85366990
EAN	4048879143271
eClass	27143423
Packaging unit	1