

## T-COUPLER SLIMLINE SHIELDED M12 MALE/ 2XM12 FEMALE

For analog sensors

T-coupler

Male straight – females straight

M12 – M12

4-pole – 3-pole

shielded

Parallel circuit

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

### Illustration



Product may differ from Image

### Approvals



\* only for products with UL/CSA approved cable

### Form

Form 42731

### Technical Data

Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Material group	IEC 60664-1, category I
Coding	A-coded
Locking of ports	Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing
Compression gland	M12 (SW13)
Protection	IP67 inserted and tightened (EN 60529)
Material	PUR

### General data

Pollution Degree	3
Temperature range	-25...+85 °C

### Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879332798
eClass	27143423
Packaging unit	1

