

M12-PANEL FEED THROUGH 6POLE A CODED


Control cabinet entry system

Male - female

M12, 6-pole

A-coded

shielded

[Link to Product](#)**Illustration**

Product may differ from Image

Form

Form 46111

General data

Pollution Degree 3

Mounting set M16×1.5 mm

Temperature range -25...+85 °C

Technical Data

Operating voltage max. 30 V AC/DC

Rated surge voltage 0.8 kV

Operating current per contact max. 4 A

Material group IEC 60664-1, category I

Coding A-coded

Locking of ports Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing

Protection IP65 and IP67 when plugged and screwed down (EN 60529)

Material Brass, nickel plated

Commercial data

country of origin CZ


customs tariff number 85366990

EAN 4048879139892

eClass 27279220

Packaging unit 1

Sketch



Product may differ from Image