


7/8" MALE FLANGE PLUG

Wire 4X0.75 1m

Flange male
7/8" (4-pole)
with multi-strand wire

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Form

Form 78321

General data

Pollution Degree	3
Material (contact)	Copper alloy
Material (contact carrier)	PUR
Material (contact surface)	Au
Temperature range	-25...+85 °C

Cables

Cable number	977
No./diameter of wires	4 × 0.75 mm ²
Wire isolation	PVC (br, wh, bl, bk)

Technical Data

Operating voltage	max. 300 V AC/DC
Operating voltage (only UL listed)	max. 600 V AC/DC
Rated surge voltage	4.0 kV
Operating current per contact	max. 7 A
Material group	IEC 60664-1, category III
Locking of ports	Screw thread 7/8" (recommended torque 1.5 Nm) self-securing
Compression gland	7/8" (SW24)
Protection	IP68 inserted and tightened (EN 60529)
Over voltage category	III

Commercial data

country of origin	DE
customs tariff number	85444290
EAN	4048879892315
eClass	27279218
Packaging unit	1