

M8 ADAPTOR ON TOP OF MSUD VALVE PLUG FORM A 18MM

Without electronics 60 V AC/DC

Form A (18 mm) – M8, connector top entry
 max. 60 V AC/DC
 without components
 3-pole

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Form

Form 88901

General data

Temperature range -25...+85 °C

Technical Data

| | |
|-------------------------------|--|
| Operating voltage | max. 60 V AC/DC |
| Operating current per contact | max. 4 A |
| Configuration | 2 contacts + bridged PE |
| Protection | IP67 inserted and tightened (EN 60529) |
| Locking of ports | M3/M8 (recommended torque 0.4 Nm) |
| Rated surge voltage | 1.5 kV |

Commercial data

| | |
|-----------------------|---------------|
| country of origin | CZ |
| customs tariff number | 85366990 |
| EAN | 4048879116039 |

eClass 27143423

Packaging unit 1