

M8 ADAPTOR ON TOP OF MSUD VALVE PLUG FORM A 18MM

LED 24 V AC/DC

Form A (18 mm) – M8, connector top entry

24 V AC/DC $\pm 25\%$

LED (yellow)

3-pole

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals**Form**

Form 88903

General data

Temperature range -25...+85 °C

Technical Data

Operating voltage	24 V AC/DC $\pm 25\%$
Operating current per contact	max. 4 A
Configuration	2 contacts + bridged PE
Protection	M3/M8 (recommended torque 0.4 Nm)
Locking of ports	M3/M8 (recommended torque 0.4 Nm)
Rated surge voltage	0.8 kV

Commercial data

country of origin	CZ
customs tariff number	85366990
EAN	4048879116022

eClass	27143423
--------	----------

Packaging unit	1
----------------	---