

M8 ADAPTOR ON TOP OF MSUD VALVE PLUG FORM A 18MM

LED+Suppression 24 V AC/DC

Form A (18 mm) – M8, connector top entry

24 V AC $\pm 20\%$ / DC $\pm 25\%$

LED and suppression

3-pole

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals**Form**

Form 88905

General data

Temperature range -25...+85 °C

Technical DataOperating voltage 24 V AC $\pm 20\%$ / DC $\pm 25\%$

Rated surge voltage 0.8 kV

Operating current per contact max. 4 A

Configuration 2 contacts + bridged PE

Switch off peak max. 55 V

Locking of ports M3/M8 (recommended torque 0.4 Nm)

Protection IP67 inserted and tightened (EN 60529)

Commercial data

country of origin CZ

customs tariff number 85366990

EAN 4048879116015

eClass 27143423

Packaging unit 1